



Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, 4/26/2019, and 67-115 (Flow Rate), 89.6-115 (Flow Rate), and 89.6-115 (Flow Rate). Rows list various eco-ATWB models and their performance metrics.



Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, Flow, and Temperature (67-115). Rows list various eco-ATWB models (e.g., eco-ATWB 9-3K9, eco-ATWB 9-4H9) and their corresponding performance metrics across a range of flow rates and temperatures.



Evapco ECO-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, 4/26/2019, and 67-115 (Flow) and 89.6-115 (Temp). Rows list various Evapco models and their performance metrics.



Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, 4/26/2019, and 67-115 for each of the 100 models. Each cell contains numerical performance data.



Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, 4/26/2019, and 67-115 for each of the 115 models. Each model row contains 48 data points representing performance metrics across various conditions.



Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, 4/26/2019, and 100+ columns of performance metrics (67-115, 89.6-115, 89.6-115, 89.6-115, First Flow, First Flow, Second Flow, Second Flow, Third Flow, Third Flow, Third Flow).



Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, 4/26/2019, and 100 columns of performance metrics (67-100). Rows list various model numbers and their corresponding values.



Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, 4/26/2019, and 100+ columns of performance metrics (67-115, 89.6-102, 98.6-102, First Flow, Second Flow, Third Flow, Third Flow). Rows include models like eco-ATWB-10-4K18, eco-ATWB-10-4L18, etc.





Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, GPM, and Flow (1st-11th) and rows for various models (eco-ATWB 20-3124 to eco-ATWB 7-6118-Z).



Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, 67-115, 89.6-102, 98.6-106, First Flow, Second Flow, Third Flow, and Third Flow. Rows include various model numbers like eco-ATWB 7-4124-Z, eco-ATWB 7-5124-Z, etc.



Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, GPM, and Flow/Inlet/Outlet temperatures (70-90) for various configurations. Includes a date '4/26/2019' in the top left corner.



Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, 4/26/2019, and 67-112. Rows list various eco-ATWB models (e.g., eco-ATWB 12-4K18-Z) and their corresponding performance metrics.



Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, 4/26/2019, and various flow rate and temperature parameters (67, 70, 72, 77, 75, 72, 75, 77, 82, 80, 77, 80, 82, 87, 85, 82, 85, 87, 92, 90, 87, 90, 92, 92, 95, 95, 92, 95, 97, 102, 100, 97, 100, 102, 107, 105, 102, 105, 107, 112, 110, 107, 110, 112, 117, 115, 89.6, 102, 98.6, 98.6, 98.6, First Flow, First Flow, Second Flow, Second Flow, Second Flow, Third Flow, Third Flow, Third Flow).



Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, GPM, PSI, and Flow (First, Second, Third, Fourth) for various temperatures (67 to 90) and flow rates (50 to 90). The table contains performance data for 100 different models, including flow rates in GPM and PSI, and flow volumes in USGPM.



Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, 4/26/2019, and various flow rates (67 to 115) and temperatures (89.6 to 98.6). The table contains performance data for various Evapco eco-ATWB models.



Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, 4/26/2019, and various flow rate and temperature parameters (67 to 115, 89.6 to 96.6, First Flow, Second Flow, Third Flow). Rows represent different coil models like eco-ATWB 16-S112-Z, etc.





Evapco eco-ATWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol Water as Process Fluid

Table with columns for Model, GPM, PSI, Inlet, and Flow for various coil configurations. Includes a sub-header for 4/26/2019 and a grid of numerical data points.