



Evapco LRWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol as Process Fluid

Table with columns for Model, 8/19/2016, and 48 temperature points (67-98.6). Rows list various LRWB models (e.g., LRWB 3-2D6, LRWB 3-2E6, etc.) and their corresponding performance values across the temperature range.



Evapco LRWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol as Process Fluid

Table with columns for Model, 8/19/2016, and 48 temperature points (67-98.6). Rows list various LRWB models (e.g., LRWB 8-5012, LRWB 8-6M12) and their corresponding performance values across the temperature range.



8/19/2016	Evapco LRWB Line Thermal Performance in USGPM - Galvanized Steel Coil - 30% Ethylene Glycol as Process Fluid																																																								
	67	70	72	77	75	72	75	77	82	80	77	80	82	87	85	82	85	87	92	90	87	90	92	97	95	92	95	97	102	100	97	100	102	107	105	102	105	107	112	110	107	110	112	117	115	89.6	102	98.6	98.6								
Model	57	60	62	65	60	62	65	67	70	65	67	70	72	75	70	72	75	77	80	75	77	80	82	85	87	80	82	85	87	90	85	87	90	92	95	97	100	95	97	100	102	105	97	100	102	105	107	110	107	110	112	117	115	89.6	90	89.6	89.6
LRWB 8-4M12-Z	105.7	202.1	255.9	288.4	133.3	148.7	240.4	301.5	335	164.9	181.9	278.2	342.5	381.4	195.1	205.2	312.5	386.8	425.5	220.3	232.4	351.4	434.7	476.3	250.2	265.1	401	488.4	526.6	282.9	302.5	450	548	579.8	322.3	342.4	509	-	-	363.3	392.8	572.2	-	-	404.8	420.1	448.3	447	362.6								
LRWB 8-4N12-Z	139.3	232.6	290.6	326	163.4	181	273.9	340.2	376.8	196.1	211	314.9	385	427.4	225	235.9	352.3	433.3	475.6	252.2	265.2	394.7	485.5	531	284.5	300.7	448.8	544.3	586	320	341.3	502.3	609.3	-	362.9	384.8	566.8	-	-	407.7	439.9	-	-	452.9	469.7	500.5	499	406.9									
LRWB 8-4O12-Z	162.7	257.8	319.7	357.5	188.3	203.4	301.8	372.7	411.8	219.3	235	345.6	420.5	465.9	249.8	261.3	385.5	472.3	517.5	278.7	292.5	430.9	528.2	576.9	313.1	330.4	488.8	591.1	-	351.1	373.8	546.2	-	-	396.9	420.4	-	-	444.9	479.3	-	-	493.3	511.2	544.2	542.6	444										
LRWB 8-5L12-Z	126.8	210.4	262.2	293.7	147.4	161.4	247.2	306.5	339.2	177.3	191.2	283.8	346.4	384.3	203.7	213.3	317.2	389.6	427.4	227.9	239.5	355.1	436.3	477	256.7	271.1	403.5	488.8	526.1	288.4	307.4	451.4	547	578.1	326.7	346.3	508.9	610.3	-	-	366.7	395.5	570.6	-	-	407.1	422.1	449.7	448.4	366							
LRWB 8-5M12-Z	143.2	228.7	283.2	316.6	164.6	180.7	267.4	330	364.6	194.7	208.5	306.1	372.2	412.3	221.6	231.7	341.4	417.9	457.9	247.1	259.3	381.4	467.3	510.3	277.5	292.7	432.5	522.8	562.3	310.9	331	483.2	584.3	-	-	351.4	372.1	544.1	-	-	393.7	424.1	609.3	-	-	436.4	452.3	481.4	480	393							
LRWB 8-5N12-Z	170.6	259.5	318.9	355.2	193.4	207.6	301.7	369.9	407.6	222.7	237.6	343.8	416	459.8	251.8	262.9	382.3	465.9	509.6	279.5	292.8	426	519.8	566.8	312.6	329.2	481.9	580.5	-	349.1	371	537.2	-	-	393.3	415.9	603.7	-	-	439.5	472.7	-	-	486.1	503.4	535.3	533.8	438.6									
LRWB 8-5O12-Z	192.8	285.3	348.8	387.7	214.9	229.9	330.3	403.4	443.7	246	261.9	375.4	452.7	499.6	277.1	288.8	416.6	506.2	552.9	306.6	320.8	463.5	563.9	-	342	359.8	523.3	-	-	381.1	404.5	582.5	-	-	428.4	452.6	-	-	477.8	513.4	-	-	527.8	546.4	580.4	578.8	477										
LRWB 8-6M12-Z	163.3	247.3	302.9	337	185.5	198.7	286.8	350.8	386.2	212.8	226.8	326.3	394.1	435.1	240.1	250.4	362.4	440.9	481.8	266	278.5	403.5	491.5	535.6	297	312.6	455.9	548.4	588.9	331.3	351.8	507.8	-	-	372.7	393.9	570.2	-	-	416.1	447.2	-	-	459.9	476.1	506.0	504.6	415.3									
LRWB 8-6N12-Z	190.6	278.7	339.4	376.6	211.5	225.9	321.8	391.7	430.3	241.2	256.4	364.9	438.9	483.8	270.9	282.1	404.4	490.1	534.8	299.1	312.7	449.2	545.4	593.5	333	350	506.4	607.5	-	370.3	392.8	563.2	-	-	415.6	438.8	-	-	462.9	497	-	-	510.8	528.5	561.2	559.6	462.1										
LRWB 8-6O12-Z	211	305	370	409.9	233.2	248.6	351.1	426	467.3	264.9	281.2	397.3	476.6	524.6	296.6	308.7	439.5	531.3	579.3	326.9	341.4	487.6	590.5	-	363.1	381.3	548.9	-	-	403.1	427.2	609.6	-	-	451.6	476.4	-	-	502.3	538.8	-	-	553.5	572.5	607.5	605.8	501.4										
LRWB 8-7M12-Z	176.9	259.6	316.2	350.9	197.1	210.5	299.8	364.9	400.8	224.7	238.9	339.9	408.9	450.7	252.4	262.8	376.7	456.5	498.2	278.7	291.3	418.4	508	552.9	310.2	326	471.7	565.9	607.1	345	365.9	524.6	-	-	387.1	408.7	588.1	-	-	431.2	463	-	-	475.8	492.3	522.7	521.3	430.5									
LRWB 8-7N12-Z	202.3	291.5	353.3	391.1	223.4	238	335.4	406.4	445.8	253.5	268.9	379.2	454.5	500.2	283.6	295	419.3	506.6	552.1	312.3	326.1	465	562.8	-	346.7	364	523.2	-	-	384.7	407.6	580.9	-	-	430.8	454.3	-	-	479	513.6	-	-	527.6	545.7	578.9	577.3	478.1										
LRWB 8-7O12-Z	222.8	318.3	384.4	424.9	245.4	261	365.2	441.3	483.4	277.5	294.1	412.1	492.8	541.7	309.8	322	455.1	548.5	597.3	340.5	355.3	504	608.8	-	377.4	395.9	566.4	-	-	418.1	442.5	-	-	467.4	492.6	-	-	519	556.1	-	-	571.1	590.5	-	-	518.1											